

SIMATIC S7/PCS7 Digital input SM 321, 16 DI; 24 V DC, 1 x 40-pole, diagnostics-capable, for contacts (wired/ not wired), NAMUR encoder, 3/4-wire Bero, with chatter monitoring; Pulse extension, open-circuit detection Interface module IM 153-2 HF or IM 153-4 HF possible



Figure similar

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
Input current	
from load voltage L+ (without load), max.	100 mA
from backplane bus 5 V DC, max.	100 mA
Power loss	
Power loss, typ.	11 W
Time stamping	
Accuracy	1 ms
Digital inputs	
Number of digital inputs	16
Input characteristic curve in accordance with IEC 61131, type 1	No
Input characteristic curve in accordance with IEC 61131, type 2	Yes

<b>Number of simultaneously controllable inputs</b>	
horizontal installation	
— up to 60 °C, max.	16
vertical installation	
— up to 40 °C, max.	16
<b>Input voltage</b>	
• Type of input voltage	DC
• Rated value (DC)	8.2 V; 8.2V/18V
<b>Input current</b>	
• for signal "1", typ.	10 mA; for NAMUR: 2.1 to 7 mA, for 10k ohm/47k ohm contact: typical 10mA, for 4 wire BEROs: typical 10 mA
<b>Input delay (for rated value of input voltage)</b>	
for standard inputs	
— at "0" to "1", min.	2.5 ms
— at "0" to "1", max.	3.5 ms
— at "1" to "0", min.	2.5 ms
— at "1" to "0", max.	3.5 ms
<b>Cable length</b>	
• shielded, max.	400 m; max. 200m with 8.2 V sensor, max. 400m with 18 V sensor
• unshielded, max.	Not permitted
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
• Hardware interrupt	Yes
<b>Diagnostic messages</b>	
• Wire-break	Yes
<b>Diagnostics indication LED</b>	
• Group error SF (red)	Yes
• Status indicator digital input (green)	Yes
<b>Potential separation</b>	
Potential separation digital inputs	
• between the channels	Yes
• between the channels, in groups of	8
• between the channels and backplane bus	Yes
<b>Isolation</b>	
Isolation tested with	600 V DC
<b>Ambient conditions</b>	
Ambient temperature during operation	
• min.	0 °C

- max.
- At cold restart, min.

60 °C

0 °C

#### Connection method

required front connector 1x 40-pin

#### Dimensions

Width 40 mm

Height 125 mm

Depth 120 mm

**last modified:** 06/19/2019